

REPORT DOCUMENTATION PAGE

AFRL-SR-BL-TR-00-

Public reporting burden for this collection of information is estimated to average 1 hour per response, including the time for reviewing the data needed, and completing and reviewing this collection of information. Send comments regarding this burden estimate reducing this burden to Washington Headquarters Services, Directorate for Information Operations and Reports, 1215 Jefferson Avenue, Washington, DC 20503

3 maintaining
instructions for
the Office of

0680

1. AGENCY USE ONLY (Leave blank)		2. REPORT DATE October 10, 2000	3. REPORT TYPE AND DATES COVERED Final, 01 May 1999 - 30 Apr 2000
4. TITLE AND SUBTITLE (DURIP 99) Instrument for Ultrafast and Photogated Spectroscopy of Materials for Hole Burning Optical Storage			5. FUNDING NUMBERS AFOSR F49620-99-1-0238 CUNY RF 47411-00-01
6. AUTHOR(S) Anshel Gorokhovskiy			
7. PERFORMING ORGANIZATION NAME(S) AND ADDRESS(ES) Department of Engineering Science and Physics, The College of Staten Island, 2800 Victory Blvd., Staten Island, NY 10314			8. PERFORMING ORGANIZATION REPORT NUMBER Final Technical Report
9. SPONSORING / MONITORING AGENCY NAME(S) AND ADDRESS(ES) AFOSR/NE 801 N. Randolph St. Room 732 Arlington VA 22203-1977			10. SPONSORING / MONITORING AGENCY REPORT NUMBER
11. SUPPLEMENTARY NOTES The views, opinions and/or findings contained in this report are those of the author(s) and should not be construed as an official AF position, policy or decision, unless so designated by other documentation			
12a. DISTRIBUTION / AVAILABILITY STATEMENT Approved for public release; distribution unlimited			12b. DISTRIBUTION CODE
13. ABSTRACT (Maximum 200 Words) The tunable ultrafast laser system with femtosecond and picosecond pulse capability and 1 kHz repetition rate has been purchased and installed. Equipment was acquired for ultrafast and photo-gated hole-burning studies of materials for frequency and time domain spectral hole burning (SHB) optical storage. The goal is directed towards more efficient novel materials for SHB optical storage and photonics devices. Initially, the instrument has been used for measurements of the fluorescence decay time for several free-based and metallo-naphthalocyanines at temperatures 300 K and 8.5 K.			
14. SUBJECT TERMS			15. NUMBER OF PAGES 5
			16. PRICE CODE
17. SECURITY CLASSIFICATION OF REPORT UNCLASSIFIED	18. SECURITY CLASSIFICATION OF THIS PAGE UNCLASSIFIED	19. SECURITY CLASSIFICATION OF ABSTRACT UNCLASSIFIED	20. LIMITATION OF ABSTRACT UL

NSN 7540-01-280-5500

DTIC QUALITY INSPECTED 4

Standard Form 298 (Rev. 2-89)
Prescribed by ANSI Std. Z39-18
298-102

**(DURIP 99) Instrument for Ultrafast and Photogated Spectroscopy
of Materials for Hole Burning Optical Storage**

Air Force Office of Scientific Research

Contract/ Grant Number: F49620-99-1-0238

A. A. Gorokhovsky

College of Staten Island/CUNY

Equipment was acquired for ultrafast and photo-gated hole-burning studies of materials for frequency and time domain spectral hole burning (SHB) optical storage. The goal is directed towards more efficient novel materials for low and high temperature operation of SHB optical storage and photonics devices. The state of the art tunable ultrafast laser system with femtosecond and picosecond pulse capability and 1 kHz repetition rate has been purchased and installed.

The following items were purchased from Spectra-Physics:

1. Millennia-Vs-P – Ultra-compact high power diode pumped solid state laser producing >5 W of CW output power at 532 nm.
2. Model 3941-M1S-USP – Regeneratively mode-locked Ti: Sapphire laser in ultra-short-pulse configuration with sub 50 fs pulse width. Requires Millennia as pump source.
3. Merlin-1-5 kHz Nd:YLF intra-cavity doubled pump laser for use with the Spitfire amplifier.
4. Spitfire-LPM-UPG – Upgrade kit for long picosecond (>2-10 ps) operation.
5. SSP – Option for single shot autocorrelator for ps measurement.
6. Model 407A-1 High power optical power meter system.
7. Spectrum Diagnostic – Tsunami diagnostics package for continuous monitoring of output wavelength and spectrum.
8. OPA-800CFP – Compact femtosecond and picosecond optical parametric amplifier for the Spitfire with tuning from 1.1 μm to 3.0 μm .
9. Model SSA-F – Single shot autocorrelator for fs measurement.
10. Spitfire-USFPM-1K – 1 kHz Tunable Ti: Sapphire regenerative amplifier with spectral mask for use with fs oscillator.

DISTRIBUTION STATEMENT A
Approved for Public Release
Distribution Unlimited

20010102 040

Prior to the purchase of this equipment, we have evaluated three laser systems from the leading manufactures of the most advanced ultrafast lasers, Clark-MRX, Coherent/Quantronix, and Spectra-Physics. We have selected the Spectra-Physics system for better performance and flexibility suitable to our research. This system is tunable in the optical communication wavelength region $1\mu\text{m} - 3\mu\text{m}$, as compared to the originally proposed system from Coherent. Items 1 to 9 were purchased using the combination of budgets of the actual grant (\$190,000) and the other AFOSR funded grant (\$26,725). Item 10 was purchased using CUNY matching funds (\$68,275).

Initially, the instrument has been used for the measurement of the fluorescence decay times of several free-based and metallo- naphthalocyanines at temperatures 300 K and 8.5 K. The experimental setup is shown in Fig. 1. To excite fluorescence, laser pulses with the length of 2 ps and wavelength 400 nm were used. Fluorescence was detected using a ultrafast photodiode and 500 MHz digital oscilloscope. Time resolution of this detection system was better than 1 ns. A typical decay curve is presented in Fig. 2 for 100 cycles of data acquisition. For system 2,11,20,29-tetra-tert-butyl-2,3-naphthalocyanine in polyvinyl butyral at 8.5 K, the decay time was found to be 3.94 ns.

The instrument will be used for the characterization of prospective materials for multi-color SHB storage inaccessible with available laser sources; in particular, for the investigation of the materials for ultrafast data readout and single shot data writing capabilities for advanced Terabits capacity optical storage and Terabits/sec rate communication devices. Also, this instrumentation will be used for studies of multiphoton gated persistent hole-burning in prospective organic and metalloorganic materials where intermediate states involve excited Stark or vibrational levels with short lifetime in the range of $10^{-11} - 10^{-12}$ sec.




Fig 1. Experimental setup for measurements of optical lifetime

M: Mirror, L: Lens, F: Color Filter, PD: Photodiode




Fig. 2. Fluorescence decay of H₂TBN at 8.5 K, under 2 pS pulse excitation at 400 nm, 1mW/cm².